

# METCUT 10

General Purpose cut-off machine









## METCUT 10

### General Purpose cut-off machine

METCUT 10 cut off machine with simple construction FRP hood, viewing widow, internal illumination, recirculation coolant system, washing jet, safety limit switch.

Chop cutting by lowering the wheel with the handle ( Z movement)







### QUICK ACTING VISE ON T SLOT TABLE

HOOD SAFETY LATCH

- Sturdy Floor model cutter for Metallographic sectioning Metals,
   Ceramic and mineral samples
- · Rust proof Steel construction
- Corrosion Resistant Cutting Chamber for a long product lifetime
- Simple Control Panel with 4 Switches Cutting, Coolant, LED light, Emergency Stop button with Door Safety Limit Switch
- Ergonomic Cutting Handle
- Easy Flow Cutting Chamber

#### **CONTROL PANEL**

- Splash Proof, corrosion resistant with see through hood
- · Cooling by two water jets to provide optimum cooling
- 0.18 KW coolant Pump
- Small opening in the side wall for long jobs
- Powerful LED light in the working area provides clear illumination

#### TECHNICAL SPECIFICATIONS

#### **MODEL: METCUT 10**

Part No. 50 02 A

10" (250mm) Wheel Size

Upto 60 mm (2.4") **Cutting Capacity** 

**Cutting Action** Z Movement Manual

3.5 Hp Three Phase Motor

Wheel Speed 3400 RPM

1.25" (32 mm) Arbor 28" X 36" X 54" **Dimensions** Weight 400 Lbs (182 kg)

220V-230V, 3Phase, 60 Hz Main

also in (480V)

**Enclosures Glaze Grey 615** Colour

Base RAL 7021

#### **ACCESSORIES**

50 02-LV **Quick Acting Vise, Left** 50 02-RV **Quick Acting Vise, RIGHT** 15 01 MB 1011 Quick clamping

Device with clamping

shoe, 90mm

#### **ACCESSORIES**

#### RUBBER BONDED ABRASIVE CUT-OFF WHEELS

Made from sheets of natural rubber and have been manufactured by the "original calendered method." They have a unique composition that makes them ideal for high quality cool, burnfree sectioning on metallographic samples

\* Please visit www.metlabcorp.com to view various sizes and descriptions

#### RESIN BONDED ABRASIVE CUT-OFF WHEELS


Uses aluminum oxide or silicon carbide particles in a bakelite binder. These wheels are especially formulated to give the ideal cut surface finish for metallographic preparations. These wheels are designated as our special 'METCUT' series.

★ Please visit www.metlabcorp.com to view various sizes and descriptions

#### **SOLUBLE OIL**

SOLUBLE OIL with rust inhibiting additive. For use with all abrasive cut-off machines and belt grinders which have contained recirculating systems. Blue, odorless, foam controlled. Sulfur and nitrate free. Mixture 40







SOLUBLE OIL

RECIRCULATING TANK

